

SPEC SHEET

Softgel Encapsulation Machine

RG0.8-110, 200, 250, 300C MODELS

INTRODUCTION

A Softgel encapsulation machine fills completely airtight sealed gelatin shells (that exist in one piece) with semi-solids or liquids. Captek softgel encapsulation machines work to the highest specification and reliability levels with unrivaled installation and after sales support.

KEYWORDS Softgel | Encapsulation | Gelatin | Capsules



ATTRIBUTES

- Large touch screen with fault diagnostic functions, operating parameter presets.
- Premium aviation aluminum alloy construction
- Fast, stable pneumatic mold pressing.
- Independent, variable drive motor, easy to adjust, low noise and smooth operation.
- Gelatin sheet cooling mechanism - low energy consumption and high refrigeration efficiency
- Net hopper for soft capsule discharge.
- The material hopper can adjust temperature, mixing speed for different product requirements.
- Functional design for easy operation and maintenance.

Whilst the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.